









Global Bladder Accumulators

BA Series – Bottom & Top Repairable





ENGINEERING YOUR SUCCESS.

Parker Has You Covered – Wherever You Are

Discover Reliable Bladder Accumulators That Fit Your **Global Footprint**

Parker's global bladder accumulators provide four standard certifications that cover three continents.

That's the largest geographical footprint of any line of standard accumulators in the market today. Whether your equipment is operating in North America, Europe or Australia, our global bladder accumulators are ready to perform. With one standard product featuring four distinct

certifications, you can trust

Parker's global bladder accumulators are specially engineered to the highest quality standards, ensuring greater productivity in your application.

that your growing bladder accumulator needs will be met - with quality and precision. **Superior Design Engineering**

We offer:

- Availability in standard sizes, including 1, 2.5, 5, 10 and 15 gallons
- **Safe Engineering Practice** designation for smaller sizes that fall below certification size or capacity
- Availability in bottom and top repairable
- Buna Nitrile, Hydrin, Butyl, **EPR and Fluoroelastomer** compounds available as standard compounds

Product Features

Parker helps reduce worry and improves efficiency with features such as:

- American Society of • **Mechanical Engineering ASME Certification**
- **CE Certification from Pressure Equipment Directive covering Europe**
- **CRN** Canadian pressure vessel certification
- AS1210 Australian certification
- Bladder repair kits are reverse compatible and can be used in traditional **ASME** only shells
- Built in the USA for rapid availability

Flexible Offering to Meet Your Requirements

Parker provides a variety of standard and optional bladders to suit a wide range of fluids and operating temperatures. The table below lists the optional bladders available, the recommended operating temperature ranges and the fluid types that are generally compatible.

Bladder Options for Global Accumulators

Product Features							
Seal Code	Polymer	Recommended Operating Temperature Range*	Maximum Temperature with Reduced Life	General Application & Compatibility**			
01	Buna-Nitrile (Standard)	-20°F to 200°F -29°C to 93°C	225°F 107°C	Standard Compound – Compatible with most mineral oil-based fluids			
04	Hydrin (Low Temperature)	-40°F to 225°F -40°C to 107°C	250°F 121°C	Compatible with most mineral oil-based fluids with enhanced low temperature performance			
06	Butyl	-40°F to 200°F -40°C to 93°C	300°F 149°C	Compatible with most phosphate ester fluids and some synthetic fluids			
08	Ethylene Propylene (EPR)	-40°F to 200°F -40°C to 93°C	300°F 149°C	Compatible with some synthetic fluids and water			
28	Fluoroelastomer	-10°F to 250°F -23°C to 121°C	400°F 204°C	Compatible with most mineral oil-based fluids at higher temperatures and some exotic fluids			

* Temperature ranges may vary depending upon the fluid used in the hydraulic system. ** Consult your local distributor or factory for fluid compatibility information.

Improve Efficiency – From Bottom to Top



Bottom Repairable 3000 psi ASME / 330 bar PED Certified Shells								
Nominal Size	Model Code	Gas Volume	Dimensions, inch (mm)					
		cu. in. (L)	A inch (mm)	B inch (mm)	Weight Ibs (kg)			
10 cu. in. (0.16L)	BAC10B3T##Y2	10.3 (.17)	11.12 (282.6)	2.00 (50.8)	3.4 (1.6)			
1 pint (0.47L)	BA001B3T##Y2	32 (.53)	9.93 (252.3)	3.50 (89.0)	5.8 (2.6)			
1 quart (0.95L)	BA002B3T##Y2	58 (.95)	10.93 (277.7)	4.49 (114.0)	9.2 (4.2)			
150 cu. in. (2.5L)	BA005B3T##Y2	155 (2.54)	18.93 (480.9)	4.49 (114.0)	16.3 (7.4)			
1 gal (3.79L)	BA01B3T##P2	222 (3.65)	17.26 (438.5)	6.61 (168.0)	29.6 (13.4)			
2.5 gal (9.46L)	BA02B3T##P2	578 (9.46)	22.21 (564.1)	8.78 (223.0)	61.5 (27.9)			
5 gal (18.9L)	BA05B3T##P2	1167 (19.1)	33.85 (859.8)	8.78 (223.0)	98 (44.5)			
10 gal (37.9L)	BA10B3T##P2	2174 (35.6)	55.46 (1409)	8.78 (223.0)	161 (73.0)			
11 gal (41.6L)	BA11B3T##P2	2419 (39.6)	59.98 (1524)	8.78 (223.0)	175 (79.4)			
15 gal (56.8L)	BA15B3T##P2	3275 (53.7)	77.85 (1978)	8.78 (223.0)	231 (104.8)			

Note: 1 gallon size available with 4000 psi Appendix 22 Approval. 2.5 gallon through 15 gallon size available with 3600 psi ASME Appendix 22 Approval.

Top Repairable 3000 psi ASME / 330 bar PED Certified Shells									
Nominal Size	Model Code	Gas Volume	Dimensions, inch (mm)						
		cu. in. (L)	A inch (mm)	B inch (mm)	Weight Ibs (kg)				
2.5 gal (9.46L)	BA02T3T##P2	571 (9.35)	20.98 (533.0)	8.78 (223.0)	66.7 (30.25)				
5 gal (18.9L)	BA05T3T##P2	1160 (18.98)	33.23 (844.1)	8.78 (223.0)	103 (46.7)				
10 gal (37.9L)	BA10T3T##P2	2167 (35.50)	54.23 (1377.5)	8.78 (223.0)	167 (75.7)				
11 gal (41.6L)	BA11T3T##P2	2412 (39.53)	59.36 (1507.7)	8.78 (223.0)	180 (81.6)				
15 gal (56.8L)	BA15T3T##P2	3269 (53.58)	77.23 (1961.7)	8.78 (223.0)	234 (106.1)				

Note: 2.5 gallon through 15 gallon size available with 3600 psi ASME Appendix 22 Approval.

Global Design Specifications

Compliance on Three Continents

Design Code Table												
		United States Design Certifications			Europe Design Certifications			Canadian & Australian Certifications				
Style	Size	Non- ASME	ASME	Non-ASME & ASME	Appendix 22 Decign	Stand. Engineering	CE	PED Design Pressure	CRN	AS 1210	CRN & AS 1210 Design Pressure	
			ASIVIL	Design Pressure	Pressure	Practice (SEP)					ASME	App. 22
	10 cu. in.	Y		3000 psi		Y		330 bar				
Bottom Repairable	1 Pint	Y		3000 psi		Y		330 bar				
	1 Quart	Y		3000 psi		Y		330 bar				
	150 cu. in.	Y		3000 psi			Υ	330 bar				
	1 Gallon		Р	3000 psi	4000 psi		Р	330 bar	Р	Р	3000 psi	4000 psi
	2.5-15 Gallon		Р	3000 psi	3600 psi		Р	330 bar	Р	Р	3000 psi	3600 psi
Top Repairable	2.5-15 Gallon		Ρ	3000 psi	3600 psi		Ρ	330 bar	Ρ	Ρ	3000 psi	3600 psi





Gas Valves

Two types of gas valves are available on the global bladder accumulator. Our standard offers a cored gas valve cartridge. We also offer a heavy duty poppet-style gas valve.

*Standard Gas Valve – Seal Compound			**Heavy Duty Poppet Style – Seal Compound				
Q	Compatible with Buna-Nitrile, Hydrin & Butyl configuration		9	Compatible with Buna-Nitrile, Hydrin & Butyl configuration			
E	Compatible with Fluoroelastomer configurations		5	Compatible with Fluoroelastomer configurations			
D	Compatible with EPR configurations		7	Compatible with EPR configurations			

Legacy Products Parker is proud to provide legacy products for these brands:





How To Order Bladder Accumulators

Ordering Parker bladder accumulators is quick and easy. Simply use the symbols in the chart below to specify your bladder accumulator and gas bottle, and then develop a model number. Select only those symbols that represent the desired features and place them in the sequence indicated by the example at the top of the chart.



MARNING - USER RESPONSIBILITY

FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise. The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors. To the extent that Parker or its subsidiaries or authorized distributors provide dot and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.



Follow the QR code to Parker's online configurator for our Global Bladder Accumulator.

Global Labels At-A-Glance

Standard Labels to Call Out All Four Certifications



1 MODEL NUMBER BA10B3T01P2 (2)Parker 3 CONADIAN REDISTRATION NUMBER LUST REG NO (CONST CODE PV 6- 196572/15 CRN R1989.5CFITG (4)5 GN PRESSURE TEMPERATURE 24,821 kPa @ 93°C ISO9001: 2000 HAZARD LEVEL M.D.M.T. @ M.A.W.P. 54°C @ 24,821 kPa (6)B IVORO TEST PRES TEST DATE 37,231 kPa 07/01/2016 (8)

1 Warning Notice per ISO 3864-2.

- 2 Nitrogen only warning.
- 3 Note to visit Parker website for details.
- 4 Warning of Accumulator under pressure per ISO 7000 symbol #3317.
- 5 Warning noting the danger of pressurized fluid injection per ISO 9244.
- 6 Warning to read technical manual per ISO 7000 symbol #1659.
- 7 ISO 1219 schematic symbol for a bladder accumulator.
- 8 Temperature range external load bearing metal components will meet per PED 2014/68/EU (formerly 97/23/EC). The ASME range is stamped on the shell. They are different.
- 9 Parker's BA Series Model Number.
- 10 The maximum operating pressure the accumulator will meet per PED 2014/68/EU (formerly 97/23/EC). The max. ASME operating pressure is stamped on the shell. They are different.
- 11 Serial number of the specific accumulator.
- 12 The internal gas capacity of the accumulator.
- 13 Parker's sales order number for the manufacturing lot. This helps customer service rapidly answer any questions pertaining to the specific accumulator.
- 14 Temperature range the internal seal components and bladder will continuously meet without rapid degradation.
- 15 The year the accumulator was manufactured.
- 16 The customer specified nitrogen pre-charge pressure. If no pre-charge is specified by the customer, this will be left blank. There will still be a holding charge of 29 psi (2 bar) inside the accumulator.
- 17 Parker's CE registration number per PED 2014/68/EU (formerly 97/23/EC). If the vessel pressure x volume (PS x V) ratio is less than 50, then the accumulator will be marked SEP for Sound Engineering Practice per Article 4.3. (Formerly Article 3.3 under 97/23/EC.)
- 18 Reminder that all ASME information is stamped on the shell.
- 19 Parker's manufacturing address.
- 1 Parker's BA Series Model Number.
- 2 Canadian Registration Number (CRN).
- 3 Australian Registration Number.
- 4 Maximum Allowable Working Pressure (MAWP) based on ASME Section VIII, Division I, Appendix 22.
- 5 Parker's Quality Management System as required by Australian AS1210.
- 6 Minimum Design Metal Temperature (MDMT) based on ASME Section VIII, Division 1, Appendix 22.
- 7 Hazard Levels A, B, C and D under Australian Standard AS4343.
- 8 Pressure the accumulator was hydrotested to (1.5 x MAWP).
- 9 Date accumulator was hydrotested.

© 2018 Parker Hannifin Corporation



USA

Parker Hannifin Corporation Accumulator & Cooler Division Americas 10711 N Second Street Machesney Park, IL 61115 phone 815 636 4100 fax 815 636 4111 www.parker.com/accumulators Europe Parker Hannifin Corporation Accumulator & Cooler Division Europe Etablissement de Colombes 16 Rue de Seine 92700 Colombes France www.parker.com

HY10-1650/US

Asia Pacific Parker Hannifin Corporation Accumulator & Cooler Division Tianjin No 21 Hongyuan Rd Xiqing Economic Development Area Tianjin China

www.parker.com

05/2018